


Philips
Laserfax
with Telephone, Copier +
SMS Function

Laserfax 925



LPF 925



fast + powerful

Laserfax

100 pages memory
14.400bps modem speed

Telephone

199 name dial entries with quick search function
Caller ID
On-Hook dialling

Copier

16 ppm copy speed
250 pages paper tray

SMS Function

Send/receive/print/save SMS messages
Broadcasting up to 10 recipients

Sudoku Function

PHILIPS

Product Specifications

Main features

Laser fax

- High speed fax with 14,4 bps modem
- ITU T30 standard/T30 new, Error Correction Modus (ECM)
- 100 pages memory
- 20 pages automatic document feeder
- 250 pages paper tray
- Polling send & receive
- Transmission report (reduction first page)
- Printing of Sudoku puzzles with solutions
- Predefined fax forms

Telephone

- 199 name dial entries with quick search function
- Group dialling: max 10 groups (up to 198 locations)
- Broadcasting: telephone entries, manual (up to 207 locations)
- Caller ID*

Copier

- 16 ppm copy speed
- Multicopy up to 99 pages
- 64 grey scales
- Zoom function (25% - 400%)

SMS function*/text2fax function**

- Send/receive/print/save/forwarding SMS messages
- Send/print text2fax messages
- Broadcasting
- Comfortable entry via alphabetical keyboard

* Depends on the availability of the service on the local operators network

** Only for countries without SMS service over the landline

General information

Power consumption

- | | |
|----------------|-------|
| · Stand by | < 8 W |
| · Transmission | 8 W |
| · Reception | 8 W |
| · Copy | 250 W |

Display

- Liquid crystal display (LCD)/two-line display with 16 characters (8x5 pixel)/European characteres/16 languages

Dimension (WxDxH)

- | | |
|------------|-----------------|
| · Unpacked | 370 x 330 x 200 |
| · Packed | 465 x 450 x 290 |

Weight

- | | |
|------------|--------|
| · Unpacked | 7,9 kg |
| · Packed | 9,6 kg |

Temperature range

- | | |
|--------------------|----------------|
| · Operation | 5° C - 35° C |
| · Storage packed | -15° C - 40° C |
| · Storage unpacked | 0 - 45° C |

Relative humidity

- | | |
|--------------------|----------|
| · Operation | 15 - 85% |
| · Storage packed | 5 - 95% |
| · Storage unpacked | 15 - 85% |

Standard package includes

- Fax machine incl. Cables (main and telephone network)
- User manual
- Document tray
- Starter Toner

Accessories

- Philips PFA 741 toner with PLUG'N'PRINT Card

9 NC	288 1XX XXX
Type number	LPF 925/XXX
EAN Code	3425160230XXX
Designed for	PSTN/PABX
Power supply	195-264V AC – 47-63 Hz

www.fax.philips.com

© 2007 SAGEM Communication Austria GmbH.
All rights reserved. The information and specifications included are subject to change without prior notice. SAGEM tries to ensure that all information in this document is correct, but does not accept liability for error or omission.

